



FOCUS POINTS

When the other vacuum pumps are stopped, SAURUS939 continues...

- Absolute safety for the process and the operators
- Absence of warm-up cycles and dead time in the process
- High resistance against powders
- High resistance against corrosion
- High endurance against condensate solvents
- High endurance against the secondary products of distillation
- Unlimited use over all the vacuum range (subject to ATEX restrictions)
- Low noise (< 70 dB)
- Low working average temperatures
- Low operative speed (250 rpm)
- Constant capability to recover the extracted solvents with incomparable efficiency
- Separation between process side and mechanical side
- Absolute sturdiness for the installation in dangerous areas
- Very limited operative costs thanks to:
 - Low-energy engines
 - new lubrication system LubriZero®
 - Simple and cheap maintenance
- ATEX certification until zone 0